

Pressure Gauge EK

Application

- Hygienic pressure measurement

Application examples

- Local display without power supply

Hygienic design/Process connection

- Direct connection for 1/2" and 1" Tri Clamp and Anderson Negele CPM CIP /SIP (cleaning up to 140 °C (284 °F) / maximum 30 minutes)
- Gauges completely made of stainless steel
- Sanitary materials and assembly fit per FDA standards
- IP 65, housing for optimized cleanability
- Conforming to 3-A Sanitary Standard 19-20
- Available version with Anderson Negele CPM fitting

Features

- Complete device is certified by 3-A SSF
- Zero adjustment
- Surface Ra < 0.2 µm (8 µ inches), finishes included in standard

Options

- Case filling with glycerine for damping
- Accessories fit with Negele Kit

Authorizations



30 bar (207 PSI) Gauge

